

# Product sheet



DAKER DK+ LEGRAND

Legrand Daker DK Plus 10kVA - UPS (rack-tower / extended battery / 3Ph In - 1Ph Out)

REF. 310178 | EAN. 3414970827005

[> Visit e-catalogue](#)

## Product characteristics

- Online Double Conversion
- 19" Rack Type
- Power Factor : 0,9
- RS232 SNMP
- Reversible screen






## The product's benefits

### Installation

- Rack and Tower usage and ultra-easy user-friendly setup

## Documentation


### TECHNICAL DOCUMENTATION

-  UPS\_LGR\_0111\_FR\_AA.pdf | PDF (0.16Mo)
-  EXB21082\_EN.pdf | PDF (11.02Mo)
-  UPS\_LGR\_0111\_GB\_AA.pdf | PDF (0.15Mo)
-  LE09706AC.pdf | PDF (15.77Mo)
-  EXB22078\_EN.pdf | PDF (4.09Mo)

### Agreements & Certificates

-  LGRP-00428-V02.01-EN.pdf | PDF (0.57Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0934.pdf | PDF (0.08Mo)