


# Product sheet



LEGRAND

Intermediate structural uprights XL<sup>3</sup> 4000 - fit onto roof base - Height 2000 mm

REF. 020520 | EAN. 3245060205201

[> Visit e-catalogue](#)

## Product characteristics

- Distribution enclosures XL<sup>3</sup> 4000 - IP 30 - IK 07 - IP 55 - IK 08 with door and sealing kit for use when joining enclosures - Consist of the combination of a "roof - base" assembly, structural uprights, functional uprights, rear and side panels RAL 7035, plinths RAL 7004 - Height 2000 or 2200 mm. - Capacity 24 modules (enclosures width 725 or width 975 with internal cable sleeve), 36 modules (enclosures width 975) - Usable faceplate height 1800 mm (1700 mm only if using the pivoting support frame) or 2000 mm
- Enclosures and cable sleeves modular metal Intermediate structural up Right - Fits on the structure of the enclosure "roof - base" - Height : 2000 mm

## Documentation

### TECHNICAL DOCUMENTATION

- [F7689A.pdf](#) | PDF (0.17Mo)
- [EXB15002\\_CA\\_XL3-4000-6300\\_EN.pdf](#) | PDF (51.43Mo)

### Agreements & Certificates

- [LOVAG-IT 12.017](#) | (0.13Mo)
- [LOVAG-IT 12.019](#) | (0.59Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0380.pdf](#) | PDF (0.14Mo)
- [ex223001\\_0383.pdf](#) | PDF (0.08Mo)