

# Product sheet



LEGRAND

MCCB DPX<sup>3</sup> 630 - thermal magnetic - 3P - Icu 36 kA (400 V~) - In 250 A

REF. 422000 | EAN. 3414970377968

> [Visit e-catalogue](#)

## Product characteristics

- DPX<sup>3</sup> 630 - thermal magnetic release MCCBs from 250 to 630 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with earth leakage modules or with residual current relays - Supplied complete with : - Fixing screws - connection plates for bars - insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures
- MCCBs thermal magnetic release - fixed version - Thermal adjustable from 0,8 to 1 In - Magnetic adjustable from 5 to 10 In. Breaking capacity Icu 36 kA (400 V~) - 3P - In : 250 A

## Documentation

### TECHNICAL DOCUMENTATION

- LE07062AB.pdf | PDF (0.81Mo)
- 📄 F01958FR01\_DPX3\_630MT\_FRAv3.pdf | PDF (0.71Mo)
- 📄 EXB15015\_TG\_Coordination\_EN.pdf | PDF (5.41Mo)
- 📄 EXB19026\_CA\_DPX3\_125HP250HP\_630\_1600EN.pdf | PDF (82.93Mo)
- 📄 F01958EN04\_DPX3630\_MT\_\_ENG.pdf | PDF (1.85Mo)
- 📄 EXB21086\_CA\_DPX3HP125\_250\_DPX3630\_1600FR.pdf | PDF (83.49Mo)

### CAD & Design specs / BIM

- 📄 422004.dwg | DWG (0.16Mo)

### CATALOGUE PAGE & OTHERS

- 📄 ex223001\_0176.pdf | PDF (0.08Mo)
- 📄 ex223001\_0194-0195.pdf | PDF (0.48Mo)
- 📄 ex223001\_0198.pdf | PDF (0.03Mo)

### Agreements & Certificates

- 📄 LGRP-00702-V01.01-EN.pdf | PDF (1.02Mo)
- 📄 OC / CB-SE-91828 | (1.11Mo)