

# Product sheet



LEGRAND

MCCB DPX<sup>3</sup> 1600 - thermal magnetic release - 4P - Icu 50 kA (400 V~) - In 630 A

REF. 422268 | EAN. 3414970380340

> [Visit e-catalogue](#)

## Product characteristics

- DPX<sup>3</sup> 1600 - thermal magnetic release MCCBs from 630 to 1250 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with residual current relays - Supplied complete with : - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures
- MCCBs thermal magnetic release fixed version - Thermal adjustable from 0,8 to 1 In - Magnetic adjustable from 5 to 10 In. Breaking capacity Icu 50 kA (400 V~) - 4P - In : 630 A

## Documentation

### TECHNICAL DOCUMENTATION

- LE07037AB.pdf | PDF (0.94Mo)
- EXB15015\_TG\_Coordination\_EN.pdf | PDF (5.41Mo)
- EXB21086\_CA\_DPX3HP125\_250\_DPX3630\_1600FR.pdf | PDF (83.49Mo)
- F01963FR01\_DPX3\_1600MT\_FRAv3.pdf | PDF (0.71Mo)
- EXB19026\_CA\_DPX3\_125HP250HP\_630\_1600EN.pdf | PDF (82.93Mo)
- F01963EN03\_DPX31600\_MT\_ENG.pdf | PDF (1.64Mo)

### CAD & Design specs / BIM

- 422267.dwg | DWG (0.18Mo)

### CATALOGUE PAGE & OTHERS

- ex223001\_0181.pdf | PDF (0.1Mo)
- ex223001\_0196-0197.pdf | PDF (0.52Mo)
- ex223001\_0198.pdf | PDF (0.03Mo)

### Agreements & Certificates

- LGRP-00819-V01.01-EN.pdf | PDF (0.64Mo)