

# Product sheet



## LEGRAND

MCCB DPX<sup>3</sup> 1600 - thermal magnetic release - 3P - Icu 70 kA (400 V~) - In 1000 A

REF. 422277 | EAN. 3414970380432

> [Visit e-catalogue](#)

## Product characteristics

- DPX<sup>3</sup> 1600 - thermal magnetic release MCCBs from 630 to 1250 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with residual current relays - Supplied complete with : - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures
- MCCBs thermal magnetic release fixed version - Thermal adjustable from 0,8 to 1 In - Magnetic adjustable from 5 to 10 In. Breaking capacity Icu 70 kA (400 V~) - 3P - In : 1000 A

## Documentation

### TECHNICAL DOCUMENTATION

- [LE07037AB.pdf](#) | PDF (0.94Mo)
- [EXB15015\\_TG\\_Coordination\\_EN.pdf](#) | PDF (5.41Mo)
- [EXB21086\\_CA\\_DPX3HP125\\_250\\_DPX3630\\_1600FR.pdf](#) | PDF (83.49Mo)
- [EXB19026\\_CA\\_DPX3\\_125HP250HP\\_630\\_1600EN.pdf](#) | PDF (82.93Mo)
- [F01963EN03\\_DPX31600\\_MT\\_ENG.pdf](#) | PDF (1.64Mo)

### CAD & Design specs / BIM

- [422274.dwg](#) | DWG (0.17Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0181.pdf](#) | PDF (0.1Mo)
- [ex223001\\_0196-0197.pdf](#) | PDF (0.52Mo)
- [ex223001\\_0198.pdf](#) | PDF (0.03Mo)

### Agreements & Certificates

- [LGRP-00819-V01.01-EN.pdf](#) | PDF (0.64Mo)