

Product sheet



LEGRAND

MCCB DPX³ 1600 - Sg elec release +central - 3P - Icu 36 kA (400 V~) - In 1600 A

REF. 422447 | EAN. 3414970382139

> [Visit e-catalogue](#)

Product characteristics

- DPX³ 1600 - Sg electronic release MCCBs from 630 to 1600 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with residual current relays - Supplied complete with : - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL³ cabinets and enclosures
- MCCBs electronic release Sg with energy metering central unit fixed version - Adjustment of Ir, Isd, Ig, tr, tsd, tg - Instantaneous protection If = 20 kA - Green indicator lamp - Connector for test unit - Logic and dynamic selectivity Breaking capacity Icu 36 kA (400 V~) - 3P - In : 1600 A

Documentation

TECHNICAL DOCUMENTATION

- LE07037AB.pdf | PDF (0.94Mo)
- 📄 F01964FR01_DPX3_1600ELE_FRAv3.pdf | PDF (0.7Mo)
- LE08865AB.pdf | PDF (5.48Mo)
- 📄 modbustable_21.pdf | PDF (0.41Mo)
- LE07038AB.pdf | PDF (1.78Mo)
- 📄 EXB20072_logic_selectivity (print).pdf | PDF (6.63Mo)
- 📄 EXB15015_TG_Coordination_EN.pdf | PDF (5.41Mo)
- 📄 EXB19026_CA_DPX3_125HP250HP_630_1600EN.pdf | PDF (82.93Mo)
- LE08866AC.pdf | PDF (6.7Mo)
- 📄 F01964EN03_DPX31600_ELE.pdf | PDF (2.99Mo)
- 📄 PRT220015_GT_selectivite_logique.pdf | PDF (6.38Mo)
- 📄 EXB21086_CA_DPX3HP125_250_DPX3630_1600FR.pdf | PDF (83.49Mo)

CAD & Design specs / BIM

- 📄 422459.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

- 📄 ex223001_0199.pdf | PDF (0.04Mo)

Software & configurators

- 📄 PowerControlStation 5.0.74.zip | ZIP (52.52Mo)



422447.dwg | DWG (0.13Mo)