

# Product sheet



LEGRAND

MCCB DPX<sup>3</sup> 1600 - Sg elec release +central - 4P - Icu 36 kA (400 V~) - In 1600 A

REF. 422453 | EAN. 3414970382191

> [Visit e-catalogue](#)

## Product characteristics

- DPX<sup>3</sup> 1600 - Sg electronic release MCCBs from 630 to 1600 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with residual current relays - Supplied complete with : - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures
- MCCBs electronic release Sg with energy metering central unit fixed version - Adjustment of Ir, Isd, Ig, tr, tsd, tg - Instantaneous protection If = 20 kA - Green indicator lamp - Connector for test unit - Logic and dynamic selectivity Breaking capacity Icu 36 kA (400 V~) - 4P - In : 1600 A

## Documentation

### TECHNICAL DOCUMENTATION

- LE07037AB.pdf | PDF (0.94Mo)
- 📄 F01964FR01\_DPX3\_1600ELE\_FRAv3.pdf | PDF (0.7Mo)
- LE08865AB.pdf | PDF (5.48Mo)
- LE07038AB.pdf | PDF (1.78Mo)
- 📄 EXB20072\_logic\_selectivity (print).pdf | PDF (6.63Mo)
- 📄 ModbusTable\_19.pdf | PDF (0.38Mo)
- 📄 EXB15015\_TG\_Coordination\_EN.pdf | PDF (5.41Mo)
- 📄 EXB19026\_CA\_DPX3\_125HP250HP\_630\_1600EN.pdf | PDF (82.93Mo)
- LE08866AC.pdf | PDF (6.7Mo)
- 📄 F01964EN03\_DPX31600\_ELE.pdf | PDF (2.99Mo)
- 📄 PRT220015\_GT\_selectivite\_logique.pdf | PDF (6.38Mo)
- 📄 EXB21086\_CA\_DPX3HP125\_250\_DPX3630\_1600FR.pdf | PDF (83.49Mo)

### CAD & Design specs / BIM

- 📄 422465.dwg | DWG (0.19Mo)

### CATALOGUE PAGE & OTHERS

- 📄 ex223001\_0199.pdf | PDF (0.04Mo)

### Software & configurators

- 📄 PowerControlStation 5.0.74.zip | ZIP (52.52Mo)



422453.dwg | DWG (0.15Mo)