

Product sheet



DPX³ 630 LEGRAND

Circuit breaker DPX3 630,4 poles, with rated current of 400A and electronic protection.

REF. 422516 | EAN. 3414970382825

[> Visit e-catalogue](#)

Product characteristics

- Breaking capacity of 36kA, according to EN/IEC standard 60947 - 2, suitable for protection of commercial and middle power installations. Rated insulation voltage of 800V Rated impulse withstand voltage of 8kV
- Compliant with NEMA AB-1. Climatic condition according to IEC/EN 60947 - 1 Annex Q, Cat. F subject to temperature, humidity, vibration, shock and salt mist.
- Protection unit with LCD screen for regulation of thermal and magnetic currents. Thermal protection within range of 0,4 - 1,0 of the rated current. Magnetic protection within range of 1,5 - 10 of the rated current.
- Can be equipped with releases (undervoltage and shunt releases) and auxiliary contacts. Can be used with rotary handles or motor operator. Locking accessories are available.
- Has different type of possible connection accessories: cage terminals, spreader and rear terminals. Is available also in a plug-in version (circuit breaker fitted with special terminals and mounted on a plug-in base). An module can be added in order to get protection against earth leakage faults.

The product's benefits

Installation

- DPX3 platform has been developed to give a new solution of protection devices for a more precise approach in power installations in order to offer the correct answer for different project needs.

Usage

- DPX3 platform provide a complete "project" approach in premium market segment, offering a range completely suitable for high power application

Avantages

- DPX3 630 is the answer for the competition in the project sub-segment. A unique size for all versions (thermal magnetic, electronic with or without measure). Earth leakage features can be achieved by adding a dedicated module at the bottom of the breaker itself.

Documentation

TECHNICAL DOCUMENTATION

- [LE07062AB.pdf](#) | PDF (0.81Mo)
- [F01959FR01_DPX3_630ELE_FRAv3.pdf](#) | PDF (1.04Mo)
- [LE08011AA.pdf](#) | PDF (0.44Mo)
- [EXB15015_TG_Coordination_EN.pdf](#) | PDF (5.41Mo)
- [EXB19026_CA_DPX3_125HP250HP_630_1600EN.pdf](#) | PDF (82.93Mo)


CATALOGUE PAGE & OTHERS

- [ex223001_0177.pdf](#) | PDF (0.06Mo)
- [ex223001_0194-0195.pdf](#) | PDF (0.48Mo)
- [ex223001_0198.pdf](#) | PDF (0.03Mo)


 F01959N04_DPX3630_ELE.pdf | PDF (3.03Mo)

 EXB21086_CA_DPX3HP125_250_DPX3630_1600FR.pdf | PDF
(83.49Mo)

CAD & Design specs / BIM

 422506.dwg | DWG (0.19Mo)

Agreements & Certificates

 OC / CB-SE-91831 | (1.1Mo)