

# Product sheet



XL<sup>3</sup> S 160 LEGRAND

Metal cabinet XL3 S 160 flush mounting 4 rows of 24 modules

REF. 337224 | EAN. 3414970897206

[> Visit e-catalogue](#)

## Product characteristics

- Allows installation of MCCBs devices type DPX3 160 (with accessory), DRX and MCBs devices
- Used to create assemblies certified IEC 61439 - 2 and - 3
- IP 30 ensuring protection against solid bodies larger than 2,5 mm
- IP40 with door ensuring protection against solid bodies larger than 1 mm
- Pre-cut sides for cable entries can receive cable ducting Lina 25

## Recommendation / Restriction

- Internal use only

## The product's benefits

### Installation

- Adjustable rail for different type of device's installation. Terminal block support provided allowing a great flexibility for earth connection.

### Usage







- Can be equipped with a transparent or reversible plain door and with different types of devices like blanking plates, clip-on holders, document holders etc..

### Avantages

- XL3 S 160 cabinets belong to the largest range of the market in this category

## Documentation



### TECHNICAL DOCUMENTATION

-  [EXB17042\\_CA\\_XL3S160\\_EN.pdf](#) | PDF (21.54Mo)
-  [EXB22022\\_CA\\_XL3S160\\_FR.pdf](#) | PDF (21.32Mo)
-  [EXB22009\\_Flipbook\\_FR\\_\(03\\_2022\).pdf](#) | PDF (6.2Mo)
-  [F02368EN-03\\_XL3S\\_160.pdf](#) | PDF (1.58Mo)
-  [LE10065AF.pdf](#) | PDF (3.05Mo)
-  [EXB22010\\_Flipbook\\_EN\\_\(03\\_2022\).pdf](#) | PDF (6.56Mo)

### CAD & Design specs / BIM

- [Legrand\\_XL<sup>3</sup>-S\\_160\\_encastré.rfa](#) | RFA (1.28Mo)

### CATALOGUE PAGE & OTHERS

-  [ex223001\\_0325.pdf](#) | PDF (0.05Mo)
-  [ex223001\\_0322.pdf](#) | PDF (0.06Mo)

### Agreements & Certificates

-  [LOVAG-IT 17.009](#) | (0.62Mo)

Legrand\_XL<sup>3</sup>-S\_160\_flush-mounting.rfa | RFA (1.27Mo)



LOVAG-IT 17.040 | (0.59Mo)



LOVAG-IT 18.117 | (1.1Mo)



LGRP-00470-V01.01-EN.pdf | PDF (1Mo)



LOVAG-IT 18.003 | (0.6Mo)