

Product sheet



XL³ S 160 LEGRAND

Metal cabinet XL3 S 160 flush mounting 8 rows of 24 modules

REF. 337228 | EAN. 3414970897244

> [Visit e-catalogue](#)

Product characteristics

- Allows installation of MCCBs devices type DPX3 160 (with accessory), DRX and MCBs devices
- Used to create assemblies certified IEC 61439 - 2 and - 3
- IP 30 ensuring protection against solid bodies larger than 2,5 mm
- IP40 with door ensuring protection against solid bodies larger than 1 mm
- Pre-cut sides for cable entries can receive cable ducting Lina 25

Recommendation / Restriction

- Internal use only

The product's benefits

Installation

- Adjustable rail for different type of device's installation. Terminal block support provided allowing a great flexibility for earth connection.

Usage

- Can be equipped with a transparent or reversible plain door and with different types of devices like blanking plates, clip-on holders, document holders etc..

Avantages

- XL3 S 160 cabinets belong to the largest range of the market in this category

Documentation

TECHNICAL DOCUMENTATION

- EXB17042_CA_XL3S160_EN.pdf | PDF (21.54Mo)
- EXB22022_CA_XL3S160_FR.pdf | PDF (21.32Mo)
- EXB22009_Flipbook_FR_(03_2022).pdf | PDF (6.2Mo)
- F02368EN-03_XL3S_160.pdf | PDF (1.58Mo)
- LE10065AF.pdf | PDF (3.05Mo)
- EXB22010_Flipbook_EN_(03_2022).pdf | PDF (6.56Mo)

CAD & Design specs / BIM

- Legrand_XL³-S_160_encastré.rfa | RFA (1.28Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0325.pdf | PDF (0.05Mo)
- ex223001_0322.pdf | PDF (0.06Mo)

Agreements & Certificates

- LOVAG-IT 17.009 | (0.62Mo)

Legrand_XL³-S_160_flush-mounting.rfa | RFA (1.27Mo)



LOVAG-IT 17.040 | (0.59Mo)



LOVAG-IT 18.117 | (1.1Mo)



LGRP-00470-V01.01-EN.pdf | PDF (1Mo)



LOVAG-IT 18.003 | (0.6Mo)