

# Product sheet



LEGRAND

Flush-mounting cabinet Practibox<sup>3</sup> - with earth - transparent door - 54 modules

REF. 401708 | EAN. 3414970336071

[> Visit e-catalogue](#)

## Product characteristics

- Flush-mounting cabinets Practibox<sup>3</sup> - from 8 to 72 modules - Class II - IP 40 - IK 07 with door - Self - extinguishing : resistance to incandescent wire 850 °C - Conform to IEC 60670 - 24 and IEC 62208 : allows to achieve assemblies conform to IEC 61439 - 3
- Flush-mounting distribution cabinets - Box for masonry or dry partitions (with dry partitions kit Cat.No 4 017 24) - Supplied with : - removable chassis with rails fitted - reversible door (door + faceplate for 1 - row cabinets ) - removable faceplates for each row (for 2, 3 and 4 - row cabinets ) - IP 2X screw terminal blocks - blanking plates (5 modules, separable per module or 1/2 module, for 2, 3 and 4 - row cabinets ) - Spacing between rails 150 mm - Door opening : 180° - Can be equipped with lock and key n° 850 Cat.No 0 019 6618 modules per row with transparent door - With earth terminal blocks - Number of rows : 3 - Number of modules : 54 - Height : 606 mm - Width : 436 mm - Depth : 91 mm

## Documentation

### TECHNICAL DOCUMENTATION

- [LE06868AA.pdf](#) | PDF (1.06Mo)
- [F01895EN-06.pdf](#) | PDF (2.12Mo)
- [F01895EN-03.pdf](#) | PDF (2.1Mo)
- [F01895FR-06.pdf](#) | PDF (2.13Mo)
- [F01895FR-03.pdf](#) | PDF (2.1Mo)

### CAD & Design specs / BIM

- [401708.dwg](#) | DWG (1.01Mo)
- [Legrand\\_Practibox<sup>3</sup>\\_18\\_modules\\_transparent\\_door.rfa](#) | RFA (2.64Mo)
- [Legrand\\_Practibox<sup>3</sup>\\_18\\_modules\\_porte\\_transparente.rfa](#) | RFA (2.64Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0316.pdf](#) | PDF (0.31Mo)
- [ex223001\\_0317.pdf](#) | PDF (0.04Mo)

### Agreements & Certificates

- [LGRP-2015-204-V1-EN.pdf](#) | PDF (0.65Mo)
- [LOVAG-IT18.019](#) | (1.04Mo)
- [OC / CB-IT-19045](#) | (0.15Mo)