

Product sheet



LEGRAND

Flush-mounting cabinet Practibox³ - with earth - white door - 18 modules

REF. 401716 | EAN. 3414970336095

[> Visit e-catalogue](#)

Product characteristics




- Flush-mounting cabinets Practibox³ - from 8 to 72 modules - Class II - IP 40 - IK 07 with door - Self - extinguishing : resistance to incandescent wire 850 °C - Conform to IEC 60670 - 24 and IEC 62208 : allows to achieve assemblies conform to IEC 61439 - 3
- Flush-mounting distribution cabinets - Box for masonry or dry partitions (with dry partitions kit Cat.No 4 017 24) - Supplied with :
 - removable chassis with rails fitted - reversible door (door + faceplate for 1 - row cabinets) - removable faceplates for each row (for 2, 3 and 4 - row cabinets) - IP 2X screw terminal blocks - blanking plates (5 modules, separable per module or 1/2 module, for 2, 3 and 4 - row cabinets) - Spacing between rails 150 mm - Door opening : 180° - Can be equipped with lock and key n° 850 Cat.No 0 019 6618 modules per row with white door RAL 9003 - With earth terminal blocks - Number of rows : 1 - Number of modules : 18 - Height : 248 mm - Width : 436 mm - Depth : 85 mm

Documentation



TECHNICAL DOCUMENTATION

-  F01895FR-06.pdf | PDF (2.13Mo)
-  F01895EN-06.pdf | PDF (2.12Mo)
-  LE09548AA-01.pdf | PDF (0.61Mo)
-  LE06867AA.pdf | PDF (0.46Mo)
-  F01895EN-03.pdf | PDF (2.1Mo)
-  F01895FR-03.pdf | PDF (2.1Mo)




CAD & Design specs / BIM

-  401716.dwg | DWG (0.63Mo)
-  Legrand_Practibox³_18_modules_white_door.rfa | RFA (2.65Mo)
-  Legrand_Practibox³_18_modules_porte_blanche.rfa | RFA (2.65Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0316.pdf | PDF (0.31Mo)
-  ex223001_0317.pdf | PDF (0.04Mo)

Agreements & Certificates

-  LGRP-2015-204-V1-EN.pdf | PDF (0.65Mo)
-  LOVAG-IT18.019 | (1.04Mo)
-  OC / CB-IT-19045 | (0.15Mo)