

# Product sheet



## LEGRAND

Flush-mounting cabinet Practibox<sup>3</sup> - with earth - white door - 36 modules

REF. 401717 | EAN. 3414970336101

[> Visit e-catalogue](#)

## Product characteristics

- Flush-mounting cabinets Practibox<sup>3</sup> - from 8 to 72 modules - Class II - IP 40 - IK 07 with door - Self - extinguishing : resistance to incandescent wire 850 °C - Conform to IEC 60670 - 24 and IEC 62208 : allows to achieve assemblies conform to IEC 61439 - 3
- Flush-mounting distribution cabinets - Box for masonry or dry partitions (with dry partitions kit Cat.No 4 017 24) - Supplied with :
  - removable chassis with rails fitted - reversible door (door + faceplate for 1 - row cabinets ) - removable faceplates for each row (for 2, 3 and 4 - row cabinets ) - IP 2X screw terminal blocks - blanking plates (5 modules, separable per module or 1/2 module, for 2, 3 and 4 - row cabinets ) - Spacing between rails 150 mm - Door opening : 180° - Can be equipped with lock and key n° 850 Cat.No 0 019 6618 modules per row with white door RAL 9003 - With earth terminal blocks - Number of rows : 2 - Number of modules : 36 - Height : 456 mm - Width : 436 mm - Depth : 85 mm

## Documentation

### TECHNICAL DOCUMENTATION

 F01895FR-06.pdf | PDF (2.13Mo)

 LE06868AA.pdf | PDF (1.06Mo)

 F01895EN-06.pdf | PDF (2.12Mo)

 F01895EN-03.pdf | PDF (2.1Mo)

 F01895FR-03.pdf | PDF (2.1Mo)

### CAD & Design specs / BIM

 401717.dwg | DWG (0.78Mo)

Legrand\_Practibox<sup>3</sup>\_18\_modules\_white\_door.rfa | RFA (2.65Mo)


Legrand\_Practibox<sup>3</sup>\_18\_modules\_porte\_blanche.rfa | RFA (2.65Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0316.pdf | PDF (0.31Mo)

 ex223001\_0317.pdf | PDF (0.04Mo)

### Agreements & Certificates

 LGRP-2015-204-V1-EN.pdf | PDF (0.65Mo)

 LOVAG-IT18.019 | (1.04Mo)

 OC / CB-IT-19045 | (0.15Mo)