

# Product sheet



PLEXO<sup>3</sup> LEGRAND

Cabinets PLEXO<sup>3</sup> - IP 65 - IK 09 - 8 modules - 1 row

REF. 601998 | EAN. 3245066019987







[> Visit e-catalogue](#)

## Product characteristics

- Shock - resistant polystyrene material
- Number of modules : 8
- Lockable door handle, sealable cover and faceplate
- Self-extinguishing: resistance to incandescent wire 650°C
- Allows to achieve assemblies conform to IEC 61 439 - 3

## Documentation



### TECHNICAL DOCUMENTATION

-  F01043FR-03.pdf | PDF (1.2Mo)
-  EXB22009\_Flipbook\_FR\_(03\_2022).pdf | PDF (6.2Mo)
-  EXB22026\_CA\_Plexo3\_FR\_imprimable.pdf | PDF (33.87Mo)
-  F01043EN-04.pdf | PDF (1.08Mo)
-  EXB14046\_CA\_Plexo3\_EN\_print.pdf | PDF (34.53Mo)
-  EXB22010\_Flipbook\_EN\_(03\_2022).pdf | PDF (6.56Mo)

### CAD & Design specs / BIM

- Legrand\_Coffret\_Plexo<sup>3</sup>\_4-8\_modules.rfa | RFA (3.01Mo)
- Legrand\_Cabinet\_Plexo<sup>3</sup>\_4-8\_modules.rfa | RFA (3.01Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0413.pdf | PDF (0.04Mo)
-  ex223001\_0412.pdf | PDF (0.11Mo)

### Agreements & Certificates

-  LOVAG-IT 17 .013-R02 | (1.1Mo)
-  OC / CB-654748 | (0.36Mo)
-  LGRP-00849-V01.01-EN.pdf | PDF (0.73Mo)