

# Product sheet



## LEGRAND

Remote trip head isolating switch DX-IS - visible load break - 3P 400 V~ - 125 A

REF. 406539 | EAN. 3245064065399

[> Visit e-catalogue](#)

## Product characteristics

- Isolating switches DX<sup>3</sup> - IS - from 16 A to 125 A - Double break contacts
- Remote trip head isolating switches - Red handle - AC 22 A, AC 23 A - Visible contact indication - Remote tripping with associated control auxiliary - Can be fitted with motorised controls and 2 DX<sup>3</sup> signalling auxiliaries - Visual indication of the actual status of the contacts : - Closed position (red indicator) - Open position (green indicator) 3P - 400 V~ - Can be equipped with add - on modules - Nominal rating In = 125 A - Number of modules : 4.5

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE03603AG.pdf](#) | PDF (1.79Mo)

[F01555EN-00.pdf](#) | PDF (0.41Mo)

[F01555FR-00.pdf](#) | PDF (0.41Mo)

### CAD & Design specs / BIM

[406538.dwg](#) | DWG (0.22Mo)

### CATALOGUE PAGE & OTHERS

[ex223001\\_0058.pdf](#) | PDF (0.09Mo)

[ex223001\\_0060.pdf](#) | PDF (0.04Mo)

### Agreements & Certificates

[OC / CB-IT-22484](#) | (0.15Mo)