

# Product sheet



## LEGRAND

140° motion sensor - IP41 - 8 m - surface-mounting - PIR technology - blister

REF. 048945 | EAN. 3414970630346

[> Visit e-catalogue](#)

## Product characteristics

- Motion sensors for 1 circuit - motion sensors for passage areas without natural light - Automatic on/off - Manual adjustment of light level threshold and time delay via potentiometer
- Ideal for passage areas PIR IP 41 wall/surface - mounting motion sensor, 140° - Blister - Range 8 m - Recommended fixing height : 2.5 m - 3 - wire with neutral - Light level threshold : 10 to 1275 lux - Adjustable time delay : 10 s to 10 min - Standby consumption : 0,75 W - For direct surface - mounting on wall

## Documentation

### TECHNICAL DOCUMENTATION

- [LE07907AC.pdf](#) | PDF (1.97Mo)
- [S000087128FR-3.pdf](#) | PDF (1.51Mo)
- [S000087128EN-2.pdf](#) | PDF (1.51Mo)

### CAD & Design specs / BIM

- [2D-LG-003513.zip](#) | ZIP (0.85Mo)

[Legrand\\_Lighting\\_Management\\_Standalone\\_Motion\\_Sensor\\_140D\\_Wall\\_Blister.rfa](#) | RFA (0.54Mo)

[Legrand\\_Gestion\\_eclairage\\_Detect\\_mvt\\_autonome\\_140D\\_Mur\\_Blister.rfa](#) | RFA (0.54Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0885.pdf](#) | PDF (0.07Mo)

### Agreements & Certificates

- [LGRP-00155-V01.01-EN.pdf](#) | PDF (0.56Mo)
- [OC / CB-685326](#) | (0.52Mo)