

# Product sheet



## LEGRAND

Sounder - IP21 - IK07 - 90 dB - 12/24/48 V= - white

REF. 040586 | EAN. 3245060405861

[> Visit e-catalogue](#)

## Product characteristics

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Sounders - Conform to EN 54 - 3 standard and CE CPR approved - IP 21 - IK 07 - Flush-mounting in false ceiling - Sound level : 90 dB at 2 meters - NF S 32 - 001 sound - Voltage range : 10 - 58 V - Average consumption : 12 V DC 5 mA - 24 V DC 9 mA - 48 V DC 13 mA

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE02620AC.pdf](#) | PDF (2.63Mo)

### Agreements & Certificates

[NFSSI Composant-DS 033 A2](#) | (0.26Mo)

[LGRP-00272-V01.01-FR.pdf](#) | PDF (0.61Mo)

### CATALOGUE PAGE & OTHERS

[ex223001\\_0921.pdf](#) | PDF (0.05Mo)