

Product sheet



LEGRAND

Sounder - IP54 - IK07 - 105 dB - 24/48 V= - white

REF. 040594 | EAN. 3245060405946

[> Visit e-catalogue](#)

Product characteristics

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Sounders - Conform to EN 54 - 3 standard and CE CPR approved - IP 54 - IK 07 - Surface - mounting - Sound level : 105 dB at 2 meters - Possibility to choose the sound, by dip switch : NF S 32 - 001 or BS 58391 (alert or alarm) or ISO 8201 or DIN =3404 - 3 or SS031711 or NEN2575 - Voltage range : 14 - 58 V - Average consumption : 24 V 140 mA - 48 V 80 mA

Documentation

TECHNICAL DOCUMENTATION

→ [LE03132-AA.pdf](#) | PDF (0.85Mo)

Agreements & Certificates

[NFSSI Composant-DS 014 A-A0](#) | (0.26Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0921.pdf](#) | PDF (0.05Mo)