

Product sheet



LEGRAND

Manipulator for call, lighting control and roller shutters

REF. 078284 | EAN. 3414971060685

> [Visit e-catalogue](#)

Product characteristics

- IP 67 waterproof manipulator : ergonomics for easy gripping
- 1 call button and a red call return indicator, visible at night thanks to 2 bright LEDs
- 1 button for controlling the reading light 1 button for ambient lighting control 2 buttons for controlling roller shutters 1 free function key (example : controlled socket)
- Antimicrobial white
- Magnetic connection between manipulator and socket: ejectability in all directions with breakout torque designed to avoid material deterioration

Recommendation / Restriction

- Equipped with a 2.5 m cord. To be associated with the socket ref. 0 782 45 or 0 782 47 and 0 782 47L

The product's benefits

Installation

- Manipulator for call, lighting control and roller shutters IP 67 waterproof manipulator: ergonomics for easy gripping 1 call button and a red call return indicator visible at night thanks to 2 bright LEDs 1 button for controlling the reading light 1 button for ambient lighting control 2 buttons for controlling roller shutters 1 free function key (example: controlled socket) Equipped with a 2.5 m cord To be associated with the socket ref. 0 782 45 or 0 782 47 and 0 782 47L Contains silver ions which limit the development of bacteria on the surface

Usage

- Contains silver ions which limit the development of bacteria on the surface

Documentation

TECHNICAL DOCUMENTATION

 LE04498AK_FR.pdf | PDF (205.67Mo)

Agreements & Certificates

 LGRP-00587-V02.01-EN.pdf | PDF (0.58Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1209.pdf | PDF (0.11Mo)