

# Product sheet



## CX<sup>3</sup> LEGRAND

Single pole latching relay - silent - 10 A - surface-mounting

REF. 049120 | EAN. 4010957491208

[> Visit e-catalogue](#)

## Product characteristics


- Pulse operated latching relays CX<sup>3</sup> Surface mounting pulse operated latching relays - 10 A - 230 V~ - 50/60 Hz - Suitable for new installations or retrofitting of existing ones - Compatible with electronic ballasts and fluocompact lamps - Mounting on plate or in flush-mounting boxes Ø 67 mm - Equipped with automatic terminals for flexible or rigid wires (max. 2.5 mm ) - Power : min. 7 W / max. 2300 W - IP 20 - IK 04 - Dimensions : 49 x 46 x 26 mm - Maximum current when used with illuminated push - buttons : 50 mA Noiseless - Single pole

## Documentation

### TECHNICAL DOCUMENTATION

→ [292389-05.pdf](#) | PDF (0.6Mo)

### Agreements & Certificates

 [VDE-40026508](#) | (0.68Mo)

 [OC / CB-DE1-67015/M1](#) | (0.11Mo)

 [NF-NF012\\_4416](#) | (0.53Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0096.pdf](#) | PDF (0.28Mo)