

# Product sheet



LEGRAND

Sounder beacons - IP65 - IK07 - 90 dB - 12/24/48 V= - red

REF. 040591 | EAN. 3245060405915

[> Visit e-catalogue](#)

## Product characteristics

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Sounder beacons - Conform to EN 54 - 3 standard and CE CPR approved - Sound level : 90 dB at 2 meters - NF S 32 - 001 sound - Red flash - Voltage range : 10 - 58 V - Average consumption : 12 V DC 23 mA ; 24 V DC 22 mA ; 48 V DC 23 mA - IP 65 - IK 07 - Surface - mounting - 2 cable glands supplied

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE02619AB.pdf](#) | PDF (1.32Mo)

### Agreements & Certificates

 [LGRP-00277-V01.01-EN.pdf](#) | PDF (0.57Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0921.pdf](#) | PDF (0.05Mo)