

Product sheet



LEGRAND

Advanced chimes and doorbell + 230V plug-in chime, 200m radio range, White, Led flash, mp3 customizable melodies

REF. 094272 | EAN. 3414971067295

[> Visit e-catalogue](#)

Product characteristics

- 200m radio range in open field to guarantee the transmission of the signal
- Sound power 80dB
- Possible to associate up to 3 additional doorbells to each chime, allowing the equipment of a place with several entrances
- 15 pre-recorded melodies on the round chime and customizable mp3 melodies on chime with flash light
- delivered with double-sided adhesive and fixing screws for easy installation

Recommendation / Restriction

- Do not expose the chime directly to the weather.

The product's benefits

Installation

- Radio transmission, battery operated doorbell and chime provide wireless installation.

Usage

- Originally, the kit allows the equipment of a big house with for example the chime functioning on battery on the ground floor and the chime to connect on sector on the first floor

Avantages

- A sober and elegant LEGRAND design that allows optimum integration into any interior.
- Kit compatible with the radio chimes COMFORT, ADVANCED and with the connected doorbell LEGRAND.
- Doorbell with reinforced protection (IP54) for greater outdoor weather resistance

Documentation

TECHNICAL DOCUMENTATION

→ [LE09950AD.pdf](#) | PDF (3.5Mo)

→ [L001835AC.pdf](#) | PDF (7.9Mo)

Agreements & Certificates

[Decl. UE RED-70-325-02](#) | (1.23Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0840.pdf](#) | PDF (0.06Mo)