

# Product sheet



SYNERGY™ LEGRAND

Synergy™ - Socket outlet - 1 gang switched - 15 A 250 V~ - Metalclad

REF. 733889 | EAN. 3245067338896

[> Visit e-catalogue](#)

## Product characteristics

- Synergy - British standard socket outlets and fused connection units - Metalclad - Front plates : grey epoxy coated steel - Terminal screws captive and backed off ready for cabling - large angled terminal entries - Supplied complete with close fit 43 mm deep surface - mounting back box
- Socket outlets 15 A - 250 V~ - Conform to BS 546 : 1950 - Patented 3 pin safety shutter mechanism - Flush-mounting back box : min. 35 mm deep - Nominal plate dimensions : 86 x 86 mm - 1 gang switched

## Documentation

### TECHNICAL DOCUMENTATION


 F02499EN-00.pdf | PDF (0.08Mo)

### Agreements & Certificates

 OC / CB-FR\_717646 | (0.34Mo)

 G-MARK-0048202300175 | (0.96Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0737.pdf | PDF (0.06Mo)