

Product sheet



SYNERGY™ LEGRAND

Synergy Authentic 1 gang unswitched socket outlet 2A
Polished Stainless steel

REF. 833259 | EAN. 3414970666741

[> Visit e-catalogue](#)

Product characteristics

- BRITISH STANDARD 2A 250V~
- 2P+E three round pins socket conform to BS546
- Screw type terminals for enhanced contacts, which accept wires up to 4mm²
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- 2P+E three round pins socket to connect lamps to a lighting circuit

Avantages

- Plate in Stainless steel rust resistance
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02267EN-00.pdf | PDF (0.63Mo)

CATALOGUE PAGE & OTHERS

ex223001_0725.pdf | PDF (0.08Mo)