

Product sheet



SYNERGY™ LEGRAND

Synergy™ Authentic - 2 gang switched double pole BS socket outlet 13A - Polished Stainless Steel

REF. 833270 | EAN. 3414970666901

[> Visit e-catalogue](#)

Product characteristics

- Switched 2X2P+E British Standard, 13A, 250V
- Conform to BS1363 - 2, ASTA Licence
- Screw type terminals for a secured & enhanced contacts
- Cover plate is 86x146 mm, product thickness is 7mm (once is installed onto the wall).
- Switch allows safe disconnection of an electrical appliance

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Monobloc complete product = ready-to-install product Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- Fitted with safety shutters to maximise child protection

Avantages

- Plate and switch rocker in same metal: Stainless steel rust resistance
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F00078FR-01-CHARTRES DECO et PRESTIGE.pdf | PDF (0.33Mo)

F02261EN-00.pdf | PDF (0.76Mo)

Agreements & Certificates

ASTA-780 | (0.28Mo)

G-MARK-LVE/2020/000875 v1 | (1.18Mo)

CATALOGUE PAGE & OTHERS

ex223001_0725.pdf | PDF (0.08Mo)