

Product sheet



SYNERGY™ LEGRAND

Synergy™ Authentic - 2 gang switched single pole BS socket outlet 13A - Polished Stainless Steel

REF. 833276 | EAN. 3414970666987

[> Visit e-catalogue](#)

Product characteristics

- 2X2P+E British Standard, 13A, 250V
- Conform to BS1363 - 2, ASTA Licence
- Screw type terminals for a secured & enhanced contacts
- Cover plate is square 86x146 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Captive terminal screws backed off ready to cabling

Usage

- Fitted with safety shutters to maximise child protection

Avantages

- Plate and switch rocker in same metal: Stainless steel rust resistance
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02260EN-00.pdf | PDF (0.7Mo)

Agreements & Certificates

G-MARK-LVE/2020/000876 v1 | (0.31Mo)

ASTA-780 | (0.28Mo)

G-MARK-LVE/2020/000876 v1 | (0.31Mo)

CATALOGUE PAGE & OTHERS

ex223001_0724.pdf | PDF (0.11Mo)