

# Product sheet



SYNERGY™ LEGRAND

Synergy™ - Socket outlet - 2 gang switched - 13 A 250 V~ - White

REF. 730076 | EAN. 3245067300763

[> Visit e-catalogue](#)

## Product characteristics


- Synergy - British standard socket outlets - white - Front plates : white thermoset - Terminal screws captive and backed off ready for cabling - large angled terminal entries - Compact mechanism for maximised wiring space - Supplied with faceplate screw caps
- Socket outlets 13 A - 250 V~ - Conform to BS 1363 : Part. 2 - For flush-mounting, back box to be min. 25 mm deep - With safety shutter mechanism - ASTA licence Single pole - switched - 2 gang - Nominal plate dimensions : 86 x 146 mm

## Documentation


### TECHNICAL DOCUMENTATION

 F00167EN-00.pdf | PDF (0.34Mo)


### Agreements & Certificates


 OC / CB-SE-90908M1 | (1.02Mo)

 ASTA-780 | (0.28Mo)

 OC / CB-SE-105240 | (0.93Mo)

 OC / CB-SE-90908 | (0.91Mo)

 LGRP-2013-234-V1-EN.pdf | PDF (1.02Mo)

 G-MARK-0048202300115 | (1.28Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0718.pdf | PDF (0.09Mo)