

Product sheet



SYNERGY™ LEGRAND

Sinergy Sleek 2 gang switched double pole BS socket outlet 13A Brushed Stainless steel

REF. 832070 | EAN. 3414970661029

[> Visit e-catalogue](#)

Product characteristics

- Switched 2X2P+E British Standard, 13A, 250V
- Conform to BS1363 - 2, ASTA Licence
- Screw type terminals for a secured & enhanced contacts
- Screwless cover plate is 86x146 mm, product thickness is 4mm (once is installed onto the wall).
- Switch allows safe disconnection of an electrical appliance

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Complete product. Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- Fitted with safety shutters to maximise child protection

Avantages

- Plate and switch rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02264EN-00.pdf | PDF (0.7Mo)

Agreements & Certificates

ASTA-780 | (0.28Mo)

G-MARK-LVE/2020/000875 v1 | (1.18Mo)

CATALOGUE PAGE & OTHERS

ex223001_0729.pdf | PDF (0.1Mo)