

Product sheet



SYNERGY™ LEGRAND

Synergy Sleek 2 gang unswitched socket outlet 13A
Polished Stainless steel

REF. 832275 | EAN. 3414970662262

> [Visit e-catalogue](#)

Product characteristics

- 2X2P+E British Standard, 13A, 250V
- Conform to BS1363 - 2, ASTA Licence
- Screw type terminals for a secured & enhanced contacts
- Screwless cover plate is 86x146 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Captive terminal screws backed off ready to cabling

Usage

- Fitted with safety shutters to maximise child protection

Avantages

- Plate and switch rocker are made in the same ferritic Stainless Steel - Grade 430, with a chromium plating which bring a better rusting resistance and a nicer finish
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02262EN-00.pdf | PDF (0.67Mo)

Agreements & Certificates

ASTA-780 | (0.28Mo)

G-MARK-LVE/2020/000875 v1 | (1.18Mo)

CATALOGUE PAGE & OTHERS

ex223001_0728.pdf | PDF (0.08Mo)