

Product sheet



SYNERGY™ LEGRAND

Socket outlet Synergy - UK/Euro-US standard - 1 gang unswitched - white

REF. 730084 | EAN. 3245067300848

[> Visit e-catalogue](#)

Product characteristics

- Synergy - Euro - US socket outlets and shaver socket - white - Front plates : white thermoset - Terminal screws captive and backed off ready for cabling - large angled terminal entries - Compact mechanism for maximised wiring space - Supplied with faceplate screw caps
- Socket outlet combined UK / Euro - US standards - For flush-mounting, back box to be min. 25 mm deep - Nominal plate dimensions : 86 x 86 mm - 1 gang unswitched - UK - 13 A / EURO - US - 16 A - 250 V~

Documentation

TECHNICAL DOCUMENTATION

 F00356EN-00.pdf | PDF (0.19Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0720.pdf | PDF (0.07Mo)