

Product sheet



SYNERGY™ LEGRAND

Double pole socket outlet Synergy - 2 gang switched - 13 A 250 V~ - metalclad

REF. 733870 | EAN. 3245067338704

[> Visit e-catalogue](#)

Product characteristics

- Synergy - British standard socket outlets and fused connection units - Metalclad - Front plates : grey epoxy coated steel - Terminal screws captive and backed off ready for cabling - large angled terminal entries - Supplied complete with close fit 43 mm deep surface - mounting back box
- Double pole socket outlets 13 A - 250 V~ - Conform to BS 1363 - Part 2 : 1995 - With safety shutter mechanism - Flush-mounting back box : min. 25 mm deep Switched - 2 gang - Nominal plate dimensions : 86 x 146 mm

Documentation

TECHNICAL DOCUMENTATION

F02498EN-00.pdf | PDF (0.07Mo)

Agreements & Certificates

ASTA-780 | (0.28Mo)

G-MARK-0048202300117 | (2.29Mo)

CATALOGUE PAGE & OTHERS

ex223001_0737.pdf | PDF (0.06Mo)