

Product sheet



SYNERGY™ LEGRAND

Sinergy Sleek 1 gang switched single pole socket outlet 5A Brushed Stainless steel

REF. 832069 | EAN. 3414970661005

[> Visit e-catalogue](#)

Product characteristics

- BRITISH STANDARD 5A 250V~
- Type D 2P+E three round pins socket conform to BS546
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- 2P+E three round pins 5A BS socket to connect lamps to a lighting circuit or moderate sized electrical appliances

Avantages


- Plate and switch rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 F02276EN-00.pdf | PDF (0.67Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0729.pdf | PDF (0.1Mo)