

# Product sheet



SYNERGY™ LEGRAND

Synergy Sleek 1 gang switched single pole socket outlet 15A Polished Stainless steel

REF. 832289 | EAN. 3414970662323

[> Visit e-catalogue](#)

## Product characteristics

- BRITISH STANDARD 15A 250V~
- Type M 2P+E three round pins socket conform to BS546
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

### Avantages

- Plate and switch rocker are made in the same ferritic Stainless Steel - Grade 430, with a chromium plating which bring a better rusting resistance and a nicer finish
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

## Documentation

### TECHNICAL DOCUMENTATION

 F02268EN-00.pdf | PDF (0.66Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0729.pdf | PDF (0.1Mo)