

Product sheet



SYNERGY™ LEGRAND

Synergy Authentic 1 gang switched single pole socket outlet 15A Brushed Stainless steel

REF. 833089 | EAN. 3414970665423

[> Visit e-catalogue](#)

Product characteristics

- BRITISH STANDARD 15A 250V~
- Type M 2P+E three round pins socket conform to BS546
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Avantages

- Plate and switch rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02265EN-00.pdf | PDF (0.72Mo)

CATALOGUE PAGE & OTHERS

ex223001_0725.pdf | PDF (0.08Mo)