

# Product sheet



LEGRAND

HRC blade type cartridge fuse - cylindrical type aM 22  
X 58 - 40 A - w indicator

REF. 016045 | EAN. 3245060160456

---

> [Visit e-catalogue](#)

## Product characteristics

- HRC blade type cartridge fuses - gG/gL and aM types
- Type aM (motor rated) - Conform to EN 60269 - 1, IEC 60269 - 1, 2 and VDE 0636 - 1 - Fully insulated end plate and handle lugs  
Size - With indicator - Rating : 100 Amps - Voltage ~ : 500 Volts - Breaking capacity : 120000 Amps

## Documentation

---

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0264.pdf](#) | PDF (0.05Mo)