

# Product sheet



## LEGRAND

HRC blade type cartridge fuse - type gG - size 00 - 40 A - with indicator

REF. 016325 | EAN. 3245060163259

[> Visit e-catalogue](#)

## Product characteristics

- HRC blade type cartridge fuses - gG/gL and aM types
- Type gG / gL - Conform to IEC 60269 - 2 - For protection against accidental contacts, use terminal shields and fuse covers supplied with protection kits Size 00 - With indicator - Rating : 40 Amps - Voltage ~ : 500 Volts - Breaking capacity : 120000 Amps

## Documentation

### TECHNICAL DOCUMENTATION

 F00189FR-06.pdf | PDF (1.52Mo)

 F00189EN-06.pdf | PDF (1.44Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0264.pdf | PDF (0.05Mo)