

# Product sheet



## ATLANTIC LEGRAND

### Atlantic steel cabinet 1000x1200x300mm - IP55 IK10

REF. 036981 | EAN. 3414970696908

> [Visit e-catalogue](#)

## Product characteristics

- IP 55 according to the standard EN/IEC 60529 : protected against dust and against jets of water from all directions
- Excellent resistance to corrosion and chemical agents thanks to textured polyester coating : 1000h resistance to salt spray
- One-piece welded body, reversible door, equipped with a cable - entry plate
- RAL 7035 suitable for industrial environments

## Recommendation / Restriction

- Recommended for industrial environments without any particular constraints.

## The product's benefits

### Installation






- Joinable cabinets. Reversible door. Double-bar lock. Equipped with universal lugs at the rear of the cabinets to facilitate the installation of accessories Autocentric of equipments

### Usage



- Can be equipped with a wide range of dedicated accessories : plain or perforated plates, plinths, cable-entry plates, plain or glass doors, etc.

## Documentation

### TECHNICAL DOCUMENTATION


-  EXB22009\_Flipbook\_FR\_(03\_2022).pdf | PDF (6.2Mo)
-  F02118FR-03.pdf | PDF (5.41Mo)
-  F02118EN-03.pdf | PDF (5.4Mo)
-  LE08301AA-01.pdf | PDF (0.77Mo)
-  EXB22010\_Flipbook\_EN\_(03\_2022).pdf | PDF (6.56Mo)

### CAD & Design specs / BIM





-  035590.dwg | DWG (0.06Mo)
-  036981.dwg | DWG (0.07Mo)

Legrand\_Atlantic\_horizontal\_version\_references\_036911\_to\_036981.rfa  
| RFA (1.29Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0416.pdf | PDF (0.06Mo)
-  ex223001\_0420-0421.pdf | PDF (0.28Mo)

### Agreements & Certificates

-  TUV GS-R 60175536 | (1.67Mo)
-  VERITAS (BV)-03212/J0 BV | (0.59Mo)
-  OC / CB-FR703246 | (0.59Mo)
-  UL listed cULus-E164087-19951122 | (0.84Mo)

Legrand\_Atlantic\_version\_horizontale\_références\_036911\_à\_036981.rfa | RFA (1.29Mo)



LGRP-2015-020-V1-EN.pdf | PDF (0.61Mo)