

Product sheet



LEGRAND

Cartridge fuse 14 x 51 mm - type gG - with stricker - 20 A

REF. 014520 | EAN. 3245060145200

[> Visit e-catalogue](#)

Product characteristics

- Rupture capacity 100000 A - Rated voltage 500V~
- Dimension 14 x 51 mm.
- Ceramic body and silver - plated contacts
- With stricker to display the fuse status (operational / blown).
- Conform to IEC/EN 60269-1 and 2, NFC 60-200.

The product's benefits

Installation

- Compatible with Legrand fuse carriers SP 51 equipped with micro-switch.

Documentation

TECHNICAL DOCUMENTATION

F00192EN-10.pdf | PDF (1.54Mo)

F00192FR-10.pdf | PDF (1.54Mo)

CATALOGUE PAGE & OTHERS

ex223001_0263.pdf | PDF (0.05Mo)

ex223001_0264.pdf | PDF (0.05Mo)

ex223001_0261.pdf | PDF (0.1Mo)