

Product sheet



LEGRAND

Control transformer and signal mono screw terminals - prim 230-400 V/sec 24 V - 630

REF. 044217 | EAN. 3245060442170

> [Visit e-catalogue](#)

Product characteristics

- Control, safety and circuit isolation transformers - single-phase - IP 2X or XXB up to 400 VA (coupling strip not mounted) - IP XXA over 400 VA - IK 04 - Conform to IEC EN 61558 - 2 - 2 and 2 - 4 or 2 - 6, UL506 and CSA C22 - 2 - No 66 - UL USA and Canada agreements - Products suitable for building equipment conforming to standards EN 61131 - 2, EN 60204 - 1 and EN 60439 - 1 - Active parts protected by cover up to 1000 VA - Interference filtering (except Cat.Nos 0 442 16/17/18) - Direct fixing possibility on symmetrical rail up to 250 VA - Supplied with coupling strip 0 V secondary / earth up to 1000 VA (except spring connection range)
- Control and safety - screw connection Input voltage = 230 V - 400 V \pm 15 V~ Output voltage = 24 V~ - Power in VA according to IEC and CSA : 630 - Power in VA according to UL : 500 - Instantaneous admissible power at $\cos \phi = 0,5$: 1500

Documentation

TECHNICAL DOCUMENTATION

- EXB22028_GT_Transformateurs_BT_BT_FR.pdf | PDF (4.83Mo)
- EXB19045_TG_Transformers_EN.pdf | PDF (4.9Mo)
- PRT219022-GT-transfosBT-BT-022020.pdf | PDF (4.27Mo)
- F00282EN-06.pdf | PDF (1.92Mo)
- F00282FR-06.pdf | PDF (1.75Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0497.pdf | PDF (0.18Mo)
- ex223001_0504.pdf | PDF (0.04Mo)
- ex223001_0494.pdf | PDF (0.1Mo)
- ex223001_0502-0503.pdf | PDF (0.06Mo)
- ex223001_0498.pdf | PDF (0.05Mo)

Agreements & Certificates

- UL recogn-20141211-E177328 | (0.4Mo)
- LGRP-2015-040-V1-EN.pdf | PDF (0.67Mo)