

Product sheet



SYNERGY™ LEGRAND

Sinergy Sleek 1 gang 2-way push button - 10A-
Brushed Stainless Steel

REF. 832007 | EAN. 3414970660466

[> Visit e-catalogue](#)

Product characteristics

- 10A
- Screw type terminals, marked for easy identification
- Large angled easy - to - access cable entries and captive screws
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- Can be used as a simple push button but can also be associated with another two-way push button, thus allowing to control a every use (door opening, door bell, timer ...) from two different control points.

Avantages


- Plate and rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 F02255EN-00.pdf | PDF (0.63Mo)

Agreements & Certificates

 ASTA-781 | (0.44Mo)

 OC / CB-FR_708093 | (0.72Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0727.pdf | PDF (0.08Mo)