

Product sheet



SYNERGY™ LEGRAND

Synergy Authentic 1 gang 2-way push button - 10A-
Brushed Stainless Steel

REF. 833007 | EAN. 3414970664501

[> Visit e-catalogue](#)

Product characteristics

- 10A
- Screw type terminals, marked for easy identification
- Large angled easy - to - access cable entries and captive screws
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- Can be used as a simple push button but can also be associated with another two-way push button, thus allowing to control a every use (door opening, door bell, timer ...) from two different control points.

Avantages

- Plate and rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02250EN-00.pdf | PDF (0.63Mo)

Agreements & Certificates

ASTA-781 | (0.44Mo)

OC / CB-FR_708093 | (0.72Mo)

CATALOGUE PAGE & OTHERS

ex223001_0722.pdf | PDF (0.09Mo)