

Product sheet



SYNERGY™ LEGRAND

Fused connection unit Synergy - unswitched + cord outlet - metalclad

REF. 733832 | EAN. 3245067338322

[> Visit e-catalogue](#)

Product characteristics


- Synergy - British standard socket outlets and fused connection units - Metalclad - Front plates : grey epoxy coated steel - Terminal screws captive and backed off ready for cabling - large angled terminal entries - Supplied complete with close fit 43 mm deep surface - mounting back box
- Fused connection units 13 A - 250 V~ - Conform to BS 1363 - Part 4 : 1995 - Fused 13 A (fuse supplied) - Fuse drawer retained by quarter turn catch, drawer padlockable in open position for safety - Flush-mounting back box : min. 25 mm deep - Nominal plate dimensions : 86 x 86 mm Unswitched - With cord outlet

Documentation

TECHNICAL DOCUMENTATION

 F02517EN-00.pdf | PDF (0.08Mo)

Agreements & Certificates

 ASTA-880 | (0.24Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0737.pdf | PDF (0.06Mo)