

Product sheet



SYNERGY™ LEGRAND

Synergy Sleek Unswitched Fused Connection Unit with cord outlet Polished Stainless Steel

REF. 832232 | EAN. 3414970661821

[> Visit e-catalogue](#)

Product characteristics

- 13A, 250V~
- Cord outlet allows the connection of an external device
- Screw type terminals for enhanced contacts accept wires up to 2X6mm²
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Compact mechanisms for maximum wiring space (back box to be min. 25mm) and slim front plates

Usage

- Fused supplied, locked captive fuse carrier (padlockable)

Avantages

- Plate is made in ferritic Stainless Steel - Grade 430, with a chromium plating which bring a better rusting resistance and a nicer finish
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02656EN-00.pdf | PDF (0.1Mo)

Agreements & Certificates

ASTA-880 | (0.24Mo)

CATALOGUE PAGE & OTHERS

ex223001_0730.pdf | PDF (0.09Mo)