


# Product sheet



SYNERGY™ LEGRAND

Synergy Authentic Unswitched Fused Connection Unit with blue LED power indicator Polished stainless Steel

REF. 833231 | EAN. 3414970666406

> [Visit e-catalogue](#)

## Product characteristics

- 13A, 250V~
- Screw type terminals for enhanced contacts accept wires up to 2X6mm<sup>2</sup>
- Marked terminals for easy identification
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- Compact mechanisms for maximum wiring space (back box to be min. 25mm) and slim front plates

### Usage

- Blue LED to indicate the status of the connected device No accessible electrical contact under the plate.

### Avantages

- Plate in Stainless steel rust resistance
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

## Documentation

### TECHNICAL DOCUMENTATION

 F00078FR-01-CHARTRES DECO et PRESTIGE.pdf | PDF (0.33Mo)

 F02655EN-00.pdf | PDF (0.05Mo)

### Agreements & Certificates

 ASTA-880 | (0.24Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0726.pdf | PDF (0.1Mo)