

# Product sheet



MOSAIC™ LEGRAND

50 mm "reduced height" floor boxes - 16 modules

REF. 088070 | EAN. 3414970330291

[> Visit e-catalogue](#)

## Product characteristics

- For raised or concrete floor from 50 to 70 mm
- Vertical wiring device positioning
- Color grey RAL 7031 ABS floor boxes, plastic handle in PA 6.6 loaded fiberglass and TPEE cable exit (elastomer)
- To be equipped with Arteor/Mosaic mechanism

## Recommendation / Restriction

- Using straight plugs recommended - Be careful when positioning sockets in their supports (earth pin on top = side outlet plugs can't be used) - Temperature of use, transport and storage: -5° à +60° - Do not use tile on the cover

## The product's benefits

### Installation

- For renovation in low depth raised floor or in concrete floor

### Usage

- Flexible cable exit for better cable protection and more resistance to the passage

### Avantages

- Easy opening by large ergonomic handle, without tool
- Delivered with toolless removable cover for coating (carpet or vinyl): easy maintenance
- Speed, robustness and functionality: facilitates the use and allows optimized cable management.

## Documentation

### TECHNICAL DOCUMENTATION

 F01912EN-03.pdf | PDF (2.72Mo)

 F01912FR-03.pdf | PDF (2.72Mo)

 LE06555AA-02.pdf | PDF (2.5Mo)

### CAD & Design specs / BIM

Legrand-reduced-height-floor-box-benelux.rfa | RFA (1.09Mo)

Legrand-reduced-height-floor-boxes-EN.rfa | RFA (1.09Mo)

legrand-boites-de-sol-hauteur-reduite-FR.rfa | RFA (1.09Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_1166.pdf | PDF (0.28Mo)