

# Product sheet



SYNERGY™ LEGRAND

Synergy™ - Rotary dimmer - 4 gang - 2 way - 400 W-100/240 V~ - 50/60 Hz - White

REF. 730049 | EAN. 3245067300497

[> Visit e-catalogue](#)

## Product characteristics

- Synergy - single pole switches, single pole push and key switches, rotary dimmers - white - Front plates : white thermoset - Terminal screws captive and backed off ready for cabling - large angled terminal entries - Compact mechanism for maximised wiring space - Supplied with faceplate screw caps
- Push on/off rotary dimmers 400 W 100 - 240 V~ - 50/60 Hz - Conform to BS EN 60669 - 1 - For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions : 86 x 146 mm - 4 gang - 2 way

## Documentation

### TECHNICAL DOCUMENTATION

→ [0064FU8-06.pdf](#) | PDF (0.44Mo)

### Agreements & Certificates

[OC / CB-SG PSB-IT-00190](#) | (0.25Mo)

### CATALOGUE PAGE & OTHERS

[ex223001\\_0717.pdf](#) | PDF (0.07Mo)