

Product sheet



SYNERGY™ LEGRAND

Synergy™ - Rotary dimmer - 1000 W- 100/240 V~ - 50/60 Hz - 1 gang

REF. 730150 | EAN. 3245067301500

[> Visit e-catalogue](#)

Product characteristics

- Synergy - single pole switches, single pole push and key switches, rotary dimmers - white - Front plates : white thermoset - Terminal screws captive and backed off ready for cabling - large angled terminal entries - Compact mechanism for maximised wiring space - Supplied with faceplate screw caps
- Push on/off rotary dimmer 1000 W 100 - 240 V/50 - 60 Hz - Conform to BS EN 60669 - 1 - For flush-mounting, back box to be min. 40 mm deep - 60 - 1000 W (230 V) - 60 - 500 W (127 V) for incandescent and halogen lamps 60 - 600 VA (230 V) - 60 - 300 VA (127 V) for halogen lamps with electronic transformers 60 - 100 VA (230 V) - 60 - 500 VA (127 V) for halogen lamps with ferromagnetic transformers - Nominal plate dimensions : 86 x 86 mm - 1 gang 2 - way

Documentation

TECHNICAL DOCUMENTATION

→ [LE03221AA.pdf](#) | PDF (0.72Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0717.pdf](#) | PDF (0.07Mo)