

Product sheet



SYNERGY™ LEGRAND

Synergy Sleek 2gang double pole switch 45A + BS 13A switched socket outlet cooker marking Glossy gold

REF. 832429 | EAN. 3414970663009

[> Visit e-catalogue](#)

Product characteristics

- 45A 250V 13A 250V~
- Screw terminals accept wires up to 16mm²
- For BS type 47 mm 2 gangs flush mounting boxes
- Screwless cover plate is square 86x146 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Compact mechanisms for maximum wiring space and slim front plates

Usage

- Complies to British Standards certifications for heavy loads. Fitted with safety shutters to maximise child protection

Avantages

- Plate and rockers are made in the same Stainless Steel - Grade 430, with a chromium plating which bring a better rusting resistance and a nicer finish
- Oblong blue led power indicator which size is 11mm x 1,5mm, LED technology ensures the maximum quality in terms of reliability, efficiency, maintenance and energy saving
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02365EN-00.pdf | PDF (0.1Mo)

Agreements & Certificates

G-MARK-0048202300179 | (1.3Mo)

OC / CB-FR_707920 | (0.58Mo)

CATALOGUE PAGE & OTHERS

ex223001_0730.pdf | PDF (0.09Mo)

