

Product sheet



SYNERGY™ LEGRAND

Synergy Authentic 2gang double pole switch 45A + BS 13A switched socket outlet cooker marking Polished Stainless steel

REF. 833229 | EAN. 3414970666369

[> Visit e-catalogue](#)

Product characteristics

- 45A 250V 13A 250V~
- Screw terminals accept wires up to 16mm²
- Flush mounting back box to be minimum 35mm deep
- Cover plate is square 86x146 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Compact mechanisms for maximum wiring space and slim front plates

Usage

- Complies to British Standards certifications for heavy loads. Fitted with safety shutters to maximise child protection

Avantages

- Plate and rockers in same metal: Stainless steel rust resistance
- Oblong blue led power indicator which size is 11mm x 1,5mm, LED technology ensures the maximum quality in terms of reliability, efficiency, maintenance and energy saving
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02658EN-00.pdf | PDF (0.11Mo)

Agreements & Certificates

G-MARK-0048202300179 | (1.3Mo)

OC / CB-FR_707920 | (0.58Mo)

CATALOGUE PAGE & OTHERS

ex223001_0726.pdf | PDF (0.1Mo)