

# Product sheet



ARTEOR™ LEGRAND

Plate Arteor - French/German std - square - 2 modules - white

REF. 576560 | EAN. 3245065765601

[> Visit e-catalogue](#)

## Product characteristics













- Arteor™ German and French standard plates - 60 mm fixing centres
- For 2 module mechanism and 1,2" touch screen - To be associated with surface mounting box Cat. No 5 723 90 or flush-mounting box Cat.No 0 800 41 and support frame Cat. No 5 760 20 (with claws) or 5 760 21 (with screws) - Square version - Neutral - White
- Neutral
- White

## Documentation

### TECHNICAL DOCUMENTATION










-  F03577EN-00.pdf | PDF (0.15Mo)
-  F00867EN-02.pdf | PDF (1.02Mo)
-  F03577FR-00.pdf | PDF (0.15Mo)

### Agreements & Certificates

-  Decl. UE RED-A 4155 A | (0.45Mo)
-  OC / CB-FR\_709182/A1 | (0.66Mo)
-  OC / CB-HU-001259-A1 | (0.54Mo)
-  OC / CB-630165/M1 | (0.48Mo)
-  OC / CB-586689/A2 | (2.25Mo)
-  OC / CB-645761A | (0.38Mo)
-  Decl. UE RED-A 4166 A | (0.45Mo)
-  OC / CB-FR\_705038/A1 | (0.67Mo)
-  Decl. UE RED-A 4048 B | (0.44Mo)
-  OC / CB-FR\_705030/A1 | (1.68Mo)
-  Decl. UE RED-A 4133 A | (0.64Mo)
-  OC / CB-DE 2-039435 | (0.66Mo)

### CAD & Design specs / BIM

-  3D\_LG-576560.stp | IFC (2.48Mo)

-  OC / CB-692865 | (1.7Mo)
-  OC / CB-583005/A1 | (0.32Mo)
-  OC / CB-FR\_717745 | (0.46Mo)
-  OC / CB-620152 | (2.22Mo)
-  OC / CB-HU-003962 | (0.48Mo)
-  OC / CB-FR\_717742 | (0.53Mo)
-  Decl. UE RED-A 4144 A | (0.45Mo)
-  Decl. UE RED-A 3812 B | (0.25Mo)
-  OC / CB-FR\_707098 | (0.67Mo)